



Catalog Number: TY5242MXR-RW
Product ID: 7TCG009130R0014
UPC Number: 78620988412
EAN Number: 05415022243550
Status: A



Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (221 F), Weather and Ultraviolet Resistant for Exterior Applications, Length of 208mm (8.19 Inches), Width of 3.6mm (0.142 Inch), Thickness of 1.04mm (0.041 Inch), Tensile Strength Rating of 180 Newtons (40 Pounds)

Actual

- Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
- Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.
- The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.
- Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.
- Application Tools: ERG50, WT1-TB

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	Railway
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
Width	0.142 in ; 3.6 mm
Length	8.19 in ; 208 mm
Thickness	0.041 in ; 1.04 mm
Material	Nylon/Polyamide 6.6
Color	Black
Lock Mechanism	Stainless Steel Barb
Tensile Strength	40 pounds ; 180 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	3.6mm
Length belt/tape/tie	208mm
Tie thickness	1.04mm
Min. holding force	180N
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None



Solvable fastener	N
MIL approval	N

Packaging

Inner Quantity	100
Inner Dimensions (inches)	12.51x5.11x.59
Outer Quantity	10000
Outer Dimensions (inches)	19.65x9.82x9.03
Weight Uom	2.2 lbs. per 1000