



Actual

Catalog Number: TY5253M-35
Product ID: 7TAG009270R0031
UPC Number: 78620999816
Status: A

Cable Tie, Maroon Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 289.7mm (11.40 Inches), Width of 4.82mm (0.19 Inches), Thickness of 1.41mm (0.055 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds)

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	High Performance
Width	0.189 in ; 4.82 mm
Length	11.4 in ; 289.7 mm
Thickness	0.055 in ; 1.4 mm
Material	Nylon/Polyamide 6.6
Color	Maroon
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 pounds ; 220 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.82mm
Length belt/tape/tie	289.7mm
Tie thickness	1.41mm
Min. holding force	222N
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Other
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y

Packaging

Inner Quantity	100
Inner Dimensions (inches)	18x1x6
Outer Quantity	500
Outer Dimensions (inches)	5x5x15
Weight Uom	0.48 lbs. per 100