



Catalog Number: TY527M-3
Product ID: 7TAG009370R0040
UPC Number: 78620993489
EAN Number: 05414363507659
Status: A



Actual

High Performance Cable Tie for Indoor Applications, Orange Color Nylon 6.6, Length of 343mm (13.5 Inches) for Bundle Diameter up to 102mm (4.02 Inches), Width of 6.9mm (0.27 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Military Specified (MIL-SPEC MS3367-3-3), 50 Pack

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	High Performance
Width	0.27 in ; 7 mm
Length	13.4 in ; 340 mm
Thickness	0.06 in ; 1.65 mm
Material	Nylon/Polyamide 6.6
Color	Orange
Lock Mechanism	Stainless Steel Barb
Tensile Strength	120 pounds ; 540 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	6.9mm
Length belt/tape/tie	343mm
Tie thickness	1.5mm
Max. bundle diameter	102mm
Min. holding force	540N
Operating temperature	-60-+85°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Orange
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	Y
UL approval	Y

Packaging

Inner Quantity	100
Inner Dimensions (inches)	18x6x1
Outer Quantity	1000
Outer Dimensions (inches)	15.25x9.5x5
Weight Uom	10 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000487
--------------------------------	-----------

