



Actual

Catalog Number: TY53510M-3
Product ID: 7TCG009400R0008
UPC Number: 78621098223
EAN Number: 05414363174370
Status: A

Cable Tie, Orange Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 889mm (35.0 Inches), Width of 8.13mm (0.32 Inches), Thickness of 1.7mm (0.07 Inches), Tensile Strength Rating of 780 Newtons (175 pounds)

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	High Performance
Width	0.32 in ; 8.13 mm
Length	35 in ; 889 mm
Thickness	0.07 in ; 1.7 mm
Material	Nylon/Polyamide 6.6
Color	Orange
Lock Mechanism	Stainless Steel Barb
Tensile Strength	175 pounds ; 780 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	8.13mm
Length belt/tape/tie	889mm
Tie thickness	1.7mm
Max. bundle diameter	80mm
Min. holding force	780N
Operating temperature	-40-+85°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Orange
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y

Packaging

Inner Quantity	50
Inner Dimensions (inches)	35x5x1
Outer Quantity	250
Outer Dimensions (inches)	38.2x5.1x5.1
Weight Uom	2.5 lbs. per 100

