

**Catalog Number:** TY5354M  
**Product ID:** 7TAG009520R0066  
**UPC Number:** 78621088637  
**EAN Number:** 05414363066132  
**Status:** A



Actual

Integrated Mounting Hole Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 371.35mm (14.62 Inches), Width of 4.83mm (0.19 Inches), Thickness of 1.4mm (0.055 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), #10 Screw for Mounting

- Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
- Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.
- The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.
- Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

#### North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5044 Mounted Head Ties
Type	Integrated Mounting Hole
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
Width	0.19 in ; 4.83 mm
Length	14.62 in ; 371.35 mm
Thickness	0.055 in ; 1.4 mm
Bundle Diameter	Max 4 in ; Max 101.6 mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 pounds ; 222 newtons

#### European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.83mm
Length belt/tape/tie	371.35mm
Tie thickness	1.4mm
Min. holding force	222N
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N



Type of fastening	Screw hole
MIL approval	N

### **Packaging**

Inner Quantity	100
Outer Quantity	500
Outer Dimensions (inches)	17x5.8x5.8
Weight Uom	10 lbs. per 1000

### **Documents / Support Tools**

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------