



Catalog Number: TY54407X
Product ID: 7TAG009550R0023
UPC Number: 78621080747
EAN Number: 05414363066439
Status: A



Actual

Hanger Strap-Releasable, Black Nylon 12 for Temperatures up to 80 Degrees Celsius (176 F), Weather and Ultraviolet Resistant, Steel, Length of 161.54mm (6.36 Inches), Width of 13.21mm (0.520 Inch), Tensile Strength Rating of 890 Newtons (200 Pounds)

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	Releasable
Width	0.52 in ; 13.21 mm
Length	6.36 in ; 151.54 mm
Bundle Diameter	2 in ; 50.8 mm
Material	Nylon/Polyamide 12
Color	Black
Lock Mechanism	Stainless Steel Barb
Tensile Strength	200 pounds ; 890 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	13.21mm
Length belt/tape/tie	161.54mm
Max. bundle diameter	50.8mm
Min. holding force	890N
Model	Internal toothing
Band closure	Steel nose
Material	Metal
Material quality	Polyamide PA
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N

Packaging

Inner Quantity	50
Outer Quantity	500
Outer Dimensions (inches)	19x14x13
Weight Uom	4.19 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website