



Actual

Catalog Number: TY54M
Product ID: 7TAG009530R0009
UPC Number: 78621082539
EAN Number: 05414363066590
Status: A

Push Mount Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 151.38mm (5.964 Inches), Width of 3.71mm (0.146 Inches), Thickness of 1.321mm (0.052 Inches), Mounting Hole Size of 4.77mm (0.188 Inches), Tensile Strength Rating of 180 Newtons (40 pounds), Bulk Pack

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5035 Push Mount Cable Ties
Type	Push Mount
Special Features	UL E49405
Width	0.14 in ; 3.71 mm
Length	5.96 in ; 151.38 mm
Thickness	0.05 In ; 1.31 mm
Bundle Diameter	Max 1.13 in ; Max 28.7 mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Stainless Steel Barb
Tensile Strength	40 pounds ; 180 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	3.71mm
Length belt/tape/tie	151.38mm
Tie thickness	1.321mm
Min. holding force	180N
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
Type of fastening	Plug-in anchor/plug-in cam
MIL approval	N

Packaging

Inner Quantity	1000
Outer Quantity	10000
Outer Dimensions (inches)	12.1x6.8x4.6
Weight Uom	1.25 lbs. per 1000