



Actual

Catalog Number: TY551M
Product ID: 7TAG009510R0065
UPC Number: 78621080642
EAN Number: 05414363066644
Status: A

Identification Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 91.44mm (3.6 Inches), Width of 2.36mm (0.093 Inch), Thickness of 25.4mm (1.0 Inch), Tensile Strength Rating of 80 Newtons (18 Pounds), Marking Pad Size of 25.4mm (1.0 Inch) x 7.95mm (0.313 Inch), Military Specified (MIL-SPEC MS3368-5-E), 100 Pack

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5040 I.D. Ties
Brand Name	Ty-Rap
Type	Identification
Standard	UL E49405
Width	0.094 in ; 2.4 mm
Length	3.62 in ; 92 mm
Thickness	0.038 in ; 0.97 mm
Bundle Diameter	0.39 to 0.63 in ; 10 to 16 mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Stainless Steel Barb
Tensile Strength	18 pounds ; 80 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	2.36mm
Length belt/tape/tie	91.44mm
Tie thickness	0.975mm
Max. bundle diameter	16mm
Min. holding force	80N
Operating temperature	-40-+85°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	Adjacent to bundle
Solvable fastener	N
VG approval	N
MIL approval	Y
UL approval	Y

Packaging

Inner Quantity	100
Outer Quantity	500
Outer Dimensions (inches)	9.7x6.3x4
Weight Uom	1 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website

Technical Drawing / Data Sheet Canada Available on Website
