



Actual

**Catalog Number:** TY5532M-Q  
**Product ID:** 7TAG009510R0068  
**UPC Number:** 78621008649  
**EAN Number:** 05414363066675  
**Status:** A

Identification Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 212.725mm (8.375 Inches), Width of 2.29mm (0.09 Inches), Thickness of 1.18mm (0.046 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), Marking Pad Size of 21.01mm (0.827 Inches) x 9.55mm (0.376 Inches), 25 Pack

**North American Specifications (UNSPSC)**

UNSPSC	39121703 Cable ties
IGCC	5040 I.D. Ties
Type	Identification
Width	0.1 in ; 2.53 mm
Length	8.375 in ; 212.725 mm
Thickness	0.046 in ; 1.18 mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Stainless Steel Barb
Tensile Strength	18 pounds ; 80 newtons

**European Specifications (ETIM)**

ETIM	EC000046 Cable tie
Band width	2.29mm
Length belt/tape/tie	212.725mm
Tie thickness	1.18mm
Min. holding force	80N
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Solvable fastener	N
MIL approval	N
UL approval	Y

**Packaging**

Inner Quantity	25
Inner Dimensions (inches)	6x1x16
Outer Quantity	500
Outer Dimensions (inches)	12x10x6.25
Weight Uom	3.75 lbs. per 1000