



Actual

Catalog Number: TYB23M
Product ID: 7TCG009450R0186
UPC Number: 78621056373
EAN Number: 05414363066996
Status: A

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 92mm (3.6 Inches), Width of 2.3mm (0.09 Inches), Thickness of 1mm (0.04 Inch), Tensile Strength Rating of 80 Newtons (18 Pounds), Work-bench Box Packaging

North American Specifications (UNSPSC)

| | |
|------------------|---|
| UNSPSC | 39121703 Cable ties |
| IGCC | 5034 Cable ties |
| Type | High Performance |
| Special Features | Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulk-heads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time. |
| Standard | UL E49405 |
| Width | 0.09 in ; 2.3 mm |
| Length | 3.6 in ; 92 mm |
| Thickness | 0.04 in ; 1 mm |
| Bundle Diameter | 0.06 to 0.63 in ; 1.5 to 16 mm |
| Material | Nylon/Polyamide 6.6 |
| Color | Natural |
| Lock Mechanism | Stainless Steel Barb |
| Tensile Strength | 18 pounds ; 80 newtons |

European Specifications (ETIM)

| | |
|---------------------------|--------------------|
| ETIM | EC000046 Cable tie |
| Band width | 2.3mm |
| Length belt/tape/tie | 92mm |
| Tie thickness | 1mm |
| Max. bundle diameter | 16mm |
| Min. holding force | 80N |
| Operating temperature | -60-+85°C |
| Model | Internal toothing |
| Band closure | Steel nose |
| Material | Plastic |
| Material quality | Polyamide PA |
| Surface protection | Untreated |
| UV-stable acc. ASTM D6779 | N |
| Halogen free | Y |
| Colour | Natural colour |
| Transparent | N |
| Reflective (fluorescent) | N |
| Text strip | None |
| Solvable fastener | N |
| VG approval | N |
| MIL approval | Y |
| UL approval | Y |

Packaging

| | |
|---------------------------|----------------|
| Inner Quantity | 1000 |
| Inner Dimensions (inches) | 4.13x4.13x3.14 |
| Outer Quantity | 10000 |



| | |
|---------------------------|--------------------|
| Outer Dimensions (inches) | 22.44x9.45x7.5 |
| Weight Uom | 5.63 lbs. per 1000 |

Documents / Support Tools

| | |
|--------------------------------|-----------|
| Technical Drawing / Data Sheet | TDS000570 |
|--------------------------------|-----------|