



Actual

Catalog Number: TYD1X15WPG6A
Product ID: 7TAA104030R0166
UPC Number: 78621009793
Status: A

Wiring Duct Wide Slot, 1 Inch x 1.5 Inches, Gray PVC, Adhesive-Backed

- Wide fingers and slots increase rigidity and enable insertion of bundles.
- V-Shaped slot lead-in enables easier and faster wire installation.
- Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.

North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Wide Slot Duct
Width	1 in ; 25.4 mm
Depth	1.5 in ; 38.1 mm
Length	6 ft ; 1.83 m
Slot Style	Wide
Adhesive Backed	Yes
Material	PVC
Color	Gray

European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	38.1mm
Width	25.4mm
Type of side wall	Slotted
Length	1829mm
Flexible	N
Type of fastening	Adhesive film
Colour	Light grey

Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x1x1.5
Outer Quantity	120
Outer Dimensions (inches)	6.6x72.3x5
Weight Uom	15.8 lbs. per 100

Header

3D Model	Available on Website
----------	----------------------