



Actual

Catalog Number: TYD1X1NPB6A
Product ID: 7TAA104040R0172
UPC Number: 78621010239
Status: A

Wiring Duct Narrow Slot, 1 Inch x 1 Inch, Black, Adhesive-Backed

- Smaller, higher number of fingers for more concise harnessing. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enable same duct for multiple applications.

North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Narrow Slot Duct
Width	1 in ; 25.4 mm
Depth	1 in ; 25.4 mm
Length	6 ft ; 1.83 m
Slot Style	Narrow
Adhesive Backed	Yes
Material	PVC
Color	Black

European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	25.4mm
Width	25.4mm
Type of side wall	Slotted
Length	1829mm
Flexible	N
Type of fastening	Adhesive film
Colour	Black

Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x1x1
Outer Quantity	120
Outer Dimensions (inches)	3.37x72.25x2
Weight Uom	13.33 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001622
--------------------------------	------------