



Representative

**Catalog Number:** TYD1X2NPW6A  
**Product ID:** 7TAA104040R0184  
**UPC Number:** 78621010085  
**Status:** A

Wiring Duct Narrow Slot, 1 Inch x 2 Inches, White, Adhesive-Backed

- Smaller, higher number of fingers for more concise harnessing. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enable same duct for multiple applications.

### North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Narrow Slot Duct
Width	1 in ; 25.4 mm
Depth	2 in ; 50.8 mm
Length	6 ft ; 1.83 m
Slot Style	Narrow
Adhesive Backed	Yes
Material	PVC
Color	White

### European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	50.8mm
Width	25.4mm
Type of side wall	Slotted
Length	1829mm
Flexible	N
Type of fastening	Adhesive film
Colour	White

### Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x1x2
Outer Quantity	120
Outer Dimensions (inches)	6.5x72x9.25
Weight Uom	23 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001622
--------------------------------	------------