



Actual

**Catalog Number:** TYD1X4NPG6  
**Product ID:** 7TAA104040R0194  
**UPC Number:** 78621009196  
**Status:** A

Wiring Duct Narrow Slot, 1 Inch x 4 Inches, Gray PVC

- Smaller, higher number of fingers for more concise harnessing. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enable same duct for multiple applications.

**North American Specifications (UNSPSC)**

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Narrow Slot Duct
Width	1 in ; 25.4 mm
Depth	4 in ; 101.6 mm
Length	6 ft ; 1.83 m
Slot Style	Narrow
Adhesive Backed	No
Material	PVC
Color	Gray

**European Specifications (ETIM)**

ETIM	EC000012 Slotted cable trunking system
Height	101.6mm
Width	25.4mm
Type of side wall	Slotted
Length	1829mm
Flexible	N
Colour	Light grey

**Packaging**

Inner Quantity	6
Inner Dimensions (inches)	72x1x4
Outer Quantity	60
Outer Dimensions (inches)	6.75x73x9.5
Weight Uom	40.67 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet	WSD-001622
--------------------------------	------------

**Header**

3D Model	Available on Website
----------	----------------------