



Representative

**Catalog Number:** TYD1X4RPG6  
**Product ID:** 7TAA104050R0072  
**UPC Number:** 78621009631  
**Status:** A

Wiring Duct Round Hole, 1 Inch x 4 Inches, Gray PVC

- Multiple rows of holes retain wire at different heights and positions with or without the cover.
- Features maximum number of wire holes.
- Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Cover attaches flush with sidewall for finished look.
- Base score line enables sidewall section to be removed.
- Integrated mounting holes - larger sizes include staggered holes for mounting flexibility.

#### North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Round Hole Duct
Width	1 in ; 25.4 mm
Depth	4 in ; 101.6 mm
Length	6 ft ; 1.83 m
Adhesive Backed	No
Material	PVC
Color	Gray

#### European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	101.6mm
Width	25.4mm
Type of side wall	Hole-/slot punching
Length	2000mm
Flexible	N
Colour	Light grey

#### Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x1x4
Outer Quantity	60
Outer Dimensions (inches)	6.75x73x9.5
Weight Uom	60 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001624
--------------------------------	------------

#### Header

3D Model	Available on Website
----------	----------------------