



Representative

**Catalog Number:** TYD25X3WPB6A  
**Product ID:** 7TAA104030R0206  
**UPC Number:** 78621010176  
**Status:** A

Wiring Duct Wide Slot, 2.5 Inches x 3 Inches, Black PVC, Adhesive-Backed

- Wide fingers and slots increase rigidity and enable insertion of bundles.
- V-Shaped slot lead-in enables easier and faster wire installation.
- Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.

#### North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Wide Slot Duct
Width	2.5 in ; 63.5 mm
Depth	3 in ; 76.2 mm
Length	6 ft ; 1.83 m
Slot Style	Wide
Adhesive Backed	Yes
Material	PVC
Color	Black

#### European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	76.2mm
Width	63.5mm
Type of side wall	Slotted
Length	1829mm
Flexible	N
Type of fastening	Adhesive film
Colour	Black

#### Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x2.5x3
Outer Quantity	60
Outer Dimensions (inches)	9x72x6.5
Weight Uom	48.25 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001623
--------------------------------	------------