



Actual

**Catalog Number:** TYD25X4NPG6A  
**Product ID:** 7TAA104040R0216  
**UPC Number:** 78621010308  
**Status:** Active

Wiring Duct Narrow Slot, 2.5 Inches x 4 Inches, Gray, Adhesive-Backed

- Smaller, higher number of fingers for more concise harnessing. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enable same duct for multiple applications.

### North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Brand Name	Ty-Duct
Type	Narrow Slot Duct
Width	2.5 in ; 63.5 mm
Depth	4 in ; 101.6 mm
Length	6 ft ; 1.83 m
Slot Style	Narrow
Adhesive Backed	Yes
Material	PVC
Color	Gray

### European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	101.6mm
Width	63.5mm
Length	1829mm
Colour	Light grey

### Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x2.5x4
Outer Quantity	60
Outer Dimensions (inches)	9.6x72x9.5
Weight Uom	68.3 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet Canada Available on Website