



Representative

**Catalog Number:** TYD2X15WPW6A  
**Product ID:** 7TAA104030R0225  
**UPC Number:** 78621009983  
**Status:** A

Wiring Duct Wide Slot, 2 Inches x 1.5 Inches, White PVC, Adhesive-Backed

- Wide fingers and slots increase rigidity and enable insertion of bundles.
- V-Shaped slot lead-in enables easier and faster wire installation.
- Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.

**North American Specifications (UNSPSC)**

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Wide Slot Duct
Width	2 in ; 50.8 mm
Depth	1.5 in ; 38.1 mm
Length	6 ft ; 1.83 m
Slot Style	Wide
Adhesive Backed	Yes
Material	PVC
Color	White

**European Specifications (ETIM)**

ETIM	EC000012 Slotted cable trunking system
Height	38.1mm
Width	50.8mm
Type of side wall	Slotted
Length	1829mm
Flexible	N
Type of fastening	Adhesive film
Colour	White

**Packaging**

Inner Quantity	6
Inner Dimensions (inches)	72x2x1.5
Outer Quantity	120
Outer Dimensions (inches)	9x72x6.5
Weight Uom	19.2 lbs. per 100