



Representative

Catalog Number: TYD2X1NPI6
Product ID: 7TAA104040R0231
UPC Number: 78621009357
Status: Active

Wiring Duct Narrow Slot, 2 Inches x 1 Inch, Intrinsic Blue PVC

- Smaller, higher number of fingers for more concise harnessing. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enable same duct for multiple applications.

North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Brand Name	Ty-Duct
Type	Narrow Slot Duct
Width	2 in ; 50.8 mm
Depth	1 in ; 25.4 mm
Length	6 ft ; 1.83 m
Slot Style	Narrow
Adhesive Backed	No
Material	PVC
Color	Intrinsic Blue

European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	25.4mm
Width	50.8mm
Length	1829mm
Colour	Blue

Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x2x1
Outer Quantity	120
Outer Dimensions (inches)	6.6x72.3x5
Weight Uom	15 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001622
Technical Drawing / Data Sheet Canada	Available on Website