



Actual

**Catalog Number:** TYD2X1WPG6A  
**Product ID:** 7TAA104030R0229  
**UPC Number:** 78621010256  
**Status:** Active

Wiring Duct Wide Slot, 2 Inches x 1 Inch, Gray PVC, Adhesive-Backed

- Wide fingers and slots increase rigidity and enable insertion of bundles.
- V-Shaped slot lead-in enables easier and faster wire installation.
- Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.

### North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Brand Name	Ty-Duct
Type	Wide Slot Duct
Width	2 in ; 50.8 mm
Depth	1 in ; 25.4 mm
Length	6 ft ; 1.83 m
Slot Style	Wide
Adhesive Backed	Yes
Material	PVC
Color	Gray

### European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	25.4mm
Width	50.8mm
Length	1829mm
Colour	Light grey

### Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x2x1
Outer Quantity	120
Outer Dimensions (inches)	6.6x72.3x5
Weight Uom	15 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet Canada [Available on Website](#)