



Representative

Catalog Number: TYD2X2WPB6A
Product ID: 7TAA104030R0234
UPC Number: 78621010181
Status: A

Wiring Duct Wide Slot, 2 Inches x 2 Inches, Black PVC, Adhesive-Backed

- Wide fingers and slots increase rigidity and enable insertion of bundles.
- V-Shaped slot lead-in enables easier and faster wire installation.
- Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.

North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Wide Slot Duct
Width	2 in ; 50.8 mm
Depth	2 in ; 50.8 mm
Length	6 ft ; 1.83 m
Slot Style	Wide
Adhesive Backed	Yes
Material	PVC
Color	Black

European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	50.8mm
Width	50.8mm
Type of side wall	Slotted
Length	1829mm
Flexible	N
Type of fastening	Adhesive film
Colour	Black

Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x2x2
Outer Quantity	120
Outer Dimensions (inches)	6.5x73x9.5
Weight Uom	28.31 lbs. per 100