



Actual

**Catalog Number:** TYD2X3SPG6NM  
**Product ID:** 7TAA104060R0205  
**UPC Number:** 78621013208  
**Status:** A

Wiring Duct Solid Wall 2 Inches X 3 Inches, PVC, Gray Duct, No Mounting Holes

- Engineered to restrict wire access.
- Improved flush sidewall and cover style for greater wire capacity.
- Versatile North American and DIN standard mounting holes enable same duct for multiple applications.
- Base score line.
- Lead-free construction.

#### North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Solid Wall Duct
Width	2.25 in ; 57.15 mm
Depth	3 in ; 76.2 mm
Length	6 ft ; 1.83 m
Mounting Holes	No
Adhesive Backed	No
Material	Rigid PVC
Color	Gray

#### European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	76.2mm
Width	57.15mm
Length	1829mm
Flexible	N
Colour	Light grey

#### Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x2x3
Outer Quantity	60
Outer Dimensions (inches)	6.5x73x9.5
Weight Uom	45 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001683
--------------------------------	------------

#### Header

3D Model	Available on Website
----------	----------------------