



Actual

Catalog Number: TYD2X4NPB6
Product ID: 7TAA104040R0248
UPC Number: 78621009286
Status: A

Wiring Duct Narrow Slot, 2 Inches x 4 Inches, Black PVC

- Smaller, higher number of fingers for more concise harnessing. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enable same duct for multiple applications.

North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Narrow Slot Duct
Width	2 in ; 50.8 mm
Depth	4 in ; 101.6 mm
Length	6 ft ; 1.83 m
Slot Style	Narrow
Adhesive Backed	No
Material	PVC
Color	Black

European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	101.6mm
Width	50.8mm
Type of side wall	Slotted
Length	1829mm
Flexible	N
Colour	Black

Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x2x4
Outer Quantity	60
Outer Dimensions (inches)	8.5x73x9.5
Weight Uom	45.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001622
--------------------------------	------------