



Actual

**Catalog Number:** TYD2X4RPW6  
**Product ID:** 7TAA104050R0090  
**UPC Number:** 78621009695  
**Status:** A

Wiring Duct Round Hole, 2 Inches x 4 Inches, White PVC

- Multiple rows of holes retain wire at different heights and positions with or without the cover.
- Features maximum number of wire holes.
- Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Cover attaches flush with sidewall for finished look.
- Base score line enables sidewall section to be removed.
- Integrated mounting holes - larger sizes include staggered holes for mounting flexibility.

#### North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Round Hole Duct
Width	2 in ; 50.8 mm
Depth	4 in ; 101.6 mm
Length	6 ft ; 1.83 m
Adhesive Backed	No
Material	PVC
Color	White

#### European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	101.6mm
Width	50.8mm
Type of side wall	Hole-/slot punching
Length	2000mm
Flexible	N
Colour	White

#### Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x2x4
Outer Quantity	60
Outer Dimensions (inches)	8.5x73x9.5
Weight Uom	60.63 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001624
--------------------------------	------------