



Representative

Catalog Number: TYD2X5WPI6
Product ID: 7TAA104030R0258
UPC Number: 78621009169
Status: A

Wiring Duct Wide Slot, 2 Inches x 5 Inches, Intrinsic Blue PVC

- Wide fingers and slots increase rigidity and enable insertion of bundles.
- V-Shaped slot lead-in enables easier and faster wire installation.
- Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.

North American Specifications (UNSPSC)

| | |
|-----------------|----------------------|
| UNSPSC | 39131712 Wiring duct |
| IGCC | 5580 Wiring duct |
| Type | Wide Slot Duct |
| Width | 2 in ; 50.8 mm |
| Depth | 5 in ; 127 mm |
| Length | 6 ft ; 1.83 m |
| Slot Style | Wide |
| Adhesive Backed | No |
| Material | PVC |
| Color | Intrinsic Blue |

European Specifications (ETIM)

| | |
|-------------------|--|
| ETIM | EC000012 Slotted cable trunking system |
| Height | 127mm |
| Width | 50.8mm |
| Type of side wall | Slotted |
| Length | 1829mm |
| Flexible | N |
| Colour | Blue |

Packaging

| | |
|---------------------------|-----------------|
| Inner Quantity | 6 |
| Inner Dimensions (inches) | 72x2x5 |
| Outer Quantity | 60 |
| Outer Dimensions (inches) | 12.6x72x9.4 |
| Weight Uom | 80 lbs. per 100 |

Documents / Support Tools

| | |
|--------------------------------|------------|
| Technical Drawing / Data Sheet | WSD-001623 |
|--------------------------------|------------|