



Representative

Catalog Number: TYD3X2NPW6
Product ID: 7TAA104040R0274
UPC Number: 78621009256
Status: A

Wiring Duct Narrow Slot, 3 Inches x 2 Inches, White PVC

- Smaller, higher number of fingers for more concise harnessing. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enable same duct for multiple applications.

North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Narrow Slot Duct
Width	3 in ; 76.2 mm
Depth	2 in ; 50.8 mm
Length	6 ft ; 1.83 m
Slot Style	Narrow
Adhesive Backed	No
Material	PVC
Color	White

European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	50.8mm
Width	76.2mm
Type of side wall	Slotted
Length	1829mm
Flexible	N
Colour	White

Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x3x2
Outer Quantity	60
Outer Dimensions (inches)	6.5x73x9.5
Weight Uom	29 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001622
--------------------------------	------------