



Representative

Catalog Number: TYD3X3NPI6
Product ID: 7TAA104040R0280
UPC Number: 78621009413
Status: Active

Wiring Duct Narrow Slot, 3 Inches x 3 Inches, Intrinsic Blue PVC

- Smaller, higher number of fingers for more concise harnessing. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enable same duct for multiple applications.

North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Brand Name	Ty-Duct
Type	Narrow Slot Duct
Width	3 in ; 76.2 mm
Depth	3 in ; 76.2 mm
Length	6 ft ; 1.83 m
Slot Style	Narrow
Adhesive Backed	No
Material	PVC
Color	Intrinsic Blue

European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	76.2mm
Width	76.2mm
Length	1829mm
Colour	Blue

Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x3x3
Outer Quantity	60
Outer Dimensions (inches)	9.5x73x10
Weight Uom	51.94 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet Canada Available on Website