



Actual

Catalog Number: TYD3X4NPG6A
Product ID: 7TAA104040R0286
UPC Number: 78621010139
Status: Active

Wiring Duct Narrow Slot, 3 Inches x 4 Inches, Gray, Adhesive-Backed

- Smaller, higher number of fingers for more concise harnessing. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enable same duct for multiple applications.

North American Specifications (UNSPSC)

| | |
|-----------------|----------------------|
| UNSPSC | 39131712 Wiring duct |
| IGCC | 5580 Wiring duct |
| Brand Name | Ty-Duct |
| Type | Narrow Slot Duct |
| Width | 3 in ; 76.2 mm |
| Depth | 4 in ; 101.6 mm |
| Length | 6 ft ; 1.83 m |
| Slot Style | Narrow |
| Adhesive Backed | Yes |
| Material | PVC |
| Color | Gray |

European Specifications (ETIM)

| | |
|--------|--|
| ETIM | EC000012 Slotted cable trunking system |
| Height | 101.6mm |
| Width | 76.2mm |
| Length | 1829mm |
| Colour | Light grey |

Packaging

| | |
|---------------------------|--------------------|
| Inner Quantity | 6 |
| Inner Dimensions (inches) | 72x3x4 |
| Outer Quantity | 60 |
| Outer Dimensions (inches) | 10x73x10 |
| Weight Uom | 73.25 lbs. per 100 |

Documents / Support Tools

Technical Drawing / Data Sheet Canada Available on Website