



Representative

**Catalog Number:** TYD3X4WPB6A  
**Product ID:** 7TAA104030R0283  
**UPC Number:** 78621010188  
**Status:** A

Wiring Duct Wide Slot, 3 Inches x 4 Inches, Black PVC, Adhesive-Backed

- Wide fingers and slots increase rigidity and enable insertion of bundles.
- V-Shaped slot lead-in enables easier and faster wire installation.
- Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.

**North American Specifications (UNSPSC)**

|                 |                      |
|-----------------|----------------------|
| UNSPSC          | 39131712 Wiring duct |
| IGCC            | 5580 Wiring duct     |
| Type            | Wide Slot Duct       |
| Width           | 3 in ; 76.2 mm       |
| Depth           | 4 in ; 101.6 mm      |
| Length          | 6 ft ; 1.83 m        |
| Slot Style      | Wide                 |
| Adhesive Backed | Yes                  |
| Material        | PVC                  |
| Color           | Black                |

**European Specifications (ETIM)**

|                   |  |
|-------------------|--|
| ETIM              | EC000012 Slotted cable trunking system |
| Height            | 101.6mm                                |
| Width             | 76.2mm                                 |
| Type of side wall | Slotted                                |
| Length            | 1829mm                                 |
| Flexible          | N                                      |
| Type of fastening | Adhesive film                          |
| Colour            | Black                                  |

**Packaging**

|                           |                    |
|---------------------------|--------------------|
| Inner Quantity            | 6                  |
| Inner Dimensions (inches) | 72x3x4             |
| Outer Quantity            | 60                 |
| Outer Dimensions (inches) | 10x73x10           |
| Weight Uom                | 73.25 lbs. per 100 |

**Documents / Support Tools**

|                                |            |
|--------------------------------|------------|
| Technical Drawing / Data Sheet | WSD-001623 |
|--------------------------------|------------|