



Representative

Catalog Number: TYD3X4WPW6A
Product ID: 7TAA104030R0288
UPC Number: 78621009999
Status: A

Wiring Duct Wide Slot, 3 Inches x 4 Inches, White PVC, Adhesive-Backed

- Wide fingers and slots increase rigidity and enable insertion of bundles.
- V-Shaped slot lead-in enables easier and faster wire installation.
- Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.

North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Wide Slot Duct
Width	3 in ; 76.2 mm
Depth	4 in ; 101.6 mm
Length	6 ft ; 1.83 m
Slot Style	Wide
Adhesive Backed	Yes
Material	PVC
Color	White

European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	101.6mm
Width	76.2mm
Type of side wall	Slotted
Length	1829mm
Flexible	N
Type of fastening	Adhesive film
Colour	White

Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x3x4
Outer Quantity	60
Outer Dimensions (inches)	10x73x10
Weight Uom	73.25 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001623
--------------------------------	------------