



Representative

**Catalog Number:** TYD4X15WPB6A  
**Product ID:** 7TAA104030R0297  
**UPC Number:** 78621010191  
**EAN Number:** 05415022477986  
**Status:** A

Wiring Duct Wide Slot, 4 Inches x 1.5 Inches, Black PVC, Adhesive-Backed

- Wide fingers and slots increase rigidity and enable insertion of bundles.
- V-Shaped slot lead-in enables easier and faster wire installation.
- Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.

### North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Wide Slot Duct
Width	4 in ; 101.6 mm
Depth	1.5 in ; 38.1 mm
Length	6 ft ; 1.83 m
Slot Style	Wide
Adhesive Backed	Yes
Material	PVC
Color	Black

### European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	38.1mm
Width	101.6mm
Type of side wall	Slotted
Length	1829mm
Flexible	N
Type of fastening	Adhesive film
Colour	Black

### Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x4x1.5
Outer Quantity	60
Outer Dimensions (inches)	9.6x72x9.5
Weight Uom	15 lbs. per 100