



Actual

Catalog Number: TYD4X3RPW6
Product ID: 7TAA104050R0114
UPC Number: 78621009701
Status: A

Wiring Duct Round Hole, 4 Inches x 3 Inches, White PVC

- Multiple rows of holes retain wire at different heights and positions with or without the cover.
- Features maximum number of wire holes.
- Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Cover attaches flush with sidewall for finished look.
- Base score line enables sidewall section to be removed.
- Integrated mounting holes - larger sizes include staggered holes for mounting flexibility.

North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Round Hole Duct
Width	4 in ; 101.6 mm
Depth	3 in ; 76.2 mm
Length	6 ft ; 1.83 m
Adhesive Backed	No
Material	PVC
Color	White

European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	76.2mm
Width	101.6mm
Type of side wall	Hole-/slot punching
Length	2000mm
Flexible	N
Colour	White

Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x4x3
Outer Quantity	60
Outer Dimensions (inches)	9.6x72x9.5
Weight Uom	53.3 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001624
--------------------------------	------------