



Representative

Catalog Number: TYD4X3WPW6A
Product ID: 7TAA104030R0316
UPC Number: 78621010003
Status: A

Wiring Duct Wide Slot, 4 Inches x 3 Inches, White PVC, Adhesive-Backed

- Wide fingers and slots increase rigidity and enable insertion of bundles.
- V-Shaped slot lead-in enables easier and faster wire installation.
- Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.

North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Wide Slot Duct
Width	4 in ; 101.6 mm
Depth	3 in ; 76.2 mm
Length	6 ft ; 1.83 m
Slot Style	Wide
Adhesive Backed	Yes
Material	PVC
Color	White

European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	76.2mm
Width	101.6mm
Type of side wall	Slotted
Length	1829mm
Flexible	N
Type of fastening	Adhesive film
Colour	White

Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x4x3
Outer Quantity	60
Outer Dimensions (inches)	9.6x72x9.5
Weight Uom	53.3 lbs. per 100