



Representative

**Catalog Number:** TYD4X4RPB6  
**Product ID:** 7TAA104050R0115  
**UPC Number:** 78621009761  
**Status:** A

Wiring Duct Round Hole, 4 Inches x 4 Inches, Black PVC

- Multiple rows of holes retain wire at different heights and positions with or without the cover.
- Features maximum number of wire holes.
- Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Cover attaches flush with sidewall for finished look.
- Base score line enables sidewall section to be removed.
- Integrated mounting holes - larger sizes include staggered holes for mounting flexibility.

**North American Specifications (UNSPSC)**

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Round Hole Duct
Width	4 in ; 101.6 mm
Depth	4 in ; 101.6 mm
Length	6 ft ; 1.83 m
Adhesive Backed	No
Material	PVC
Color	Black

**European Specifications (ETIM)**

ETIM	EC000012 Slotted cable trunking system
Height	101.6mm
Width	101.6mm
Type of side wall	Hole-/slot punching
Length	2000mm
Flexible	N
Colour	Black

**Packaging**

Inner Quantity	6
Inner Dimensions (inches)	72x4x4
Outer Quantity	30
Outer Dimensions (inches)	9.5x72x10
Weight Uom	80 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet	WSD-001624
--------------------------------	------------