



Representative

Catalog Number: TYD4X5WPB6
Product ID: 7TAA104030R0324
UPC Number: 78621009128
Status: A

Wiring Duct Wide Slot, 4 Inches x 5 Inches, Black PVC

- Wide fingers and slots increase rigidity and enable insertion of bundles.
- V-Shaped slot lead-in enables easier and faster wire installation.
- Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.

North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Wide Slot Duct
Width	4 in ; 101.6 mm
Depth	5 in ; 127 mm
Length	6 ft ; 1.83 m
Slot Style	Wide
Adhesive Backed	No
Material	PVC
Color	Black

European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	127mm
Width	101.6mm
Type of side wall	Slotted
Length	1829mm
Flexible	N
Colour	Black

Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x4x5
Outer Quantity	30
Outer Dimensions (inches)	9.5x73x13
Weight Uom	93.13 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001623
--------------------------------	------------