



Actual

**Catalog Number:** TYD4X5WPG6A  
**Product ID:** 7TAA104030R0327  
**UPC Number:** 78621010290  
**Status:** A

Wiring Duct Wide Slot, 4 Inches x 5 Inches, Gray PVC, Adhesive-Backed

- Wide fingers and slots increase rigidity and enable insertion of bundles.
- V-Shaped slot lead-in enables easier and faster wire installation.
- Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.

**North American Specifications (UNSPSC)**

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Wide Slot Duct
Width	4 in ; 101.6 mm
Depth	5 in ; 127 mm
Length	6 ft ; 1.83 m
Slot Style	Wide
Adhesive Backed	Yes
Material	PVC
Color	Gray

**European Specifications (ETIM)**

ETIM	EC000012 Slotted cable trunking system
Height	127mm
Width	101.6mm
Type of side wall	Slotted
Length	1829mm
Flexible	N
Type of fastening	Adhesive film
Colour	Light grey

**Packaging**

Inner Quantity	6
Inner Dimensions (inches)	72x4x5
Outer Quantity	30
Outer Dimensions (inches)	9.5x73x13
Weight Uom	93.13 lbs. per 100

**Header**

3D Model	Available on Website
----------	----------------------