



Actual

**Catalog Number:** TYD75X15NPB6  
**Product ID:** 7TAA104040R0327  
**UPC Number:** 78621009265  
**Status:** A

Wiring Duct Narrow Slot, 0.75 Inch x 1.5 Inches, Black PVC

**North American Specifications (UNSPSC)**

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Narrow Slot Duct
Width	0.75 in ; 19.05 mm
Depth	15 in ; 381 mm
Length	6 ft ; 1.83 m
Slot Style	Narrow
Adhesive Backed	No
Material	PVC
Color	Black

**European Specifications (ETIM)**

ETIM	EC000012 Slotted cable trunking system
Height	38.1mm
Width	19.05mm
Type of side wall	Slotted
Length	1829mm
Flexible	N
Colour	Black

**Packaging**

Inner Quantity	6
Inner Dimensions (inches)	72x.75x1.5
Outer Quantity	120
Outer Dimensions (inches)	3.75x73x6.75
Weight Uom	13.5 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet	WSD-001622
--------------------------------	------------