



Actual

**Catalog Number:** TYD75X15NPG6A  
**Product ID:** 7TAA104040R0330  
**UPC Number:** 78621009804  
**Status:** A

Wiring Duct Narrow Slot, 0.75 Inch x 1.5 Inches, Gray, Adhesive-Backed

- Smaller, higher number of fingers for more concise harnessing. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enable same duct for multiple applications.

#### North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Narrow Slot Duct
Width	0.75 in ; 19.05 mm
Depth	1.5 in ; 38.1 mm
Length	6 ft ; 1.83 m
Slot Style	Narrow
Adhesive Backed	Yes
Material	PVC
Color	Gray

#### European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	38.1mm
Width	19.05mm
Type of side wall	Slotted
Length	1829mm
Flexible	N
Type of fastening	Adhesive film
Colour	Light grey

#### Packaging

Inner Quantity	6
Inner Dimensions (inches)	72x.75x1.5
Outer Quantity	120
Outer Dimensions (inches)	3.75x73x6.75
Weight Uom	13.17 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001622
--------------------------------	------------

#### Header

3D Model	Available on Website
----------	----------------------

