



Actual

**Catalog Number:** TYD75X2WPG6  
**Product ID:** 7TAA104030R0351  
**UPC Number:** 78621008992  
**Status:** A

Wiring Duct Wide Slot, 0.75 Inch x 2 Inches, Gray PVC

- Wide fingers and slots increase rigidity and enable insertion of bundles.
- V-Shaped slot lead-in enables easier and faster wire installation.
- Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.

**North American Specifications (UNSPSC)**

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Type	Wide Slot Duct
Width	0.75 in ; 19.05 mm
Depth	2 in ; 50.8 mm
Length	6 ft ; 1.83 m
Slot Style	Wide
Adhesive Backed	No
Material	PVC
Color	Gray

**European Specifications (ETIM)**

ETIM	EC000012 Slotted cable trunking system
Height	50.8mm
Width	19.05mm
Type of side wall	Slotted
Length	1829mm
Flexible	N
Colour	Light grey

**Packaging**

Inner Quantity	6
Inner Dimensions (inches)	72x.75x2
Outer Quantity	120
Outer Dimensions (inches)	6.6x72.3x5
Weight Uom	22.5 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet	WSD-001623
--------------------------------	------------

**Header**

3D Model	Available on Website
----------	----------------------

