



Catalog Number: TYF535M
Product ID: 7TCG009520R0077
UPC Number: 78621049367
EAN Number: 05414363067313
Status: A



Actual

Integrated Mounting Hole Cable Tie - Side Mount, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 185mm (7.3 Inches), Width of Width of 4.6mm (0.18 Inch), Thickness of 1mm (0.04 Inches), Mounting Hole Size of 4.0mm (0.157 Inches), Tensile Strength Rating of 222 Newtons (50 pounds), 100 Pack

- Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
- Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.
- The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.
- Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5044 Mounted Head Ties
Type	Integrated Mounting Hole
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
Width	0.19 in ; 4.8 mm
Length	7.3 in ; 185 mm
Thickness	0.04 in ; 1 mm
Bundle Diameter	0.12 to 1.77 in ; 3 to 45 mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 pounds ; 222 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.8mm
Length belt/tape/tie	185mm
Tie thickness	1mm
Max. bundle diameter	45mm
Min. holding force	222N
Operating temperature	-40-+85°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Natural colour



Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
Type of fastening	Screw hole
VG approval	N
MIL approval	N
UL approval	N

Packaging

Inner Quantity	100
Outer Quantity	4000
Outer Dimensions (inches)	19.7x10.2x9.1
Weight Uom	3.13 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000577
--------------------------------	-----------