



**Catalog Number:** TYH24M  
**Product ID:** 7TAG009590R0004  
**UPC Number:** 78621081096  
**EAN Number:** 05414363067399  
**Status:** A



Cable Tie, Heat Stabilized Polyamide (Nylon 6.6) - Greenish Tint for Temperatures up to 105 Degrees Celsius (221 F) for Indoor Applications, Length of 138mm (5.4 Inches), Width of 3.6mm (0.14 Inch), Thickness of 1.3mm (0.05 Inch), Maximum Bundle Diameter 35mm (1.38 Inch), Tensile Strength Rating of 180 Newtons (40 Pounds)

- Application Tools: ERG50, WT1-TB

Actual

### North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	Heat-Stabilized
Standard	UL E49405
Width	0.14 in ; 3.56 mm
Length	5.4 in ; 138 mm
Thickness	0.05 in ; 1.3 mm
Bundle Diameter	Max 1.38 in ; Max 35 mm
Material	Nylon/Polyamide 6.6
Color	Green
Lock Mechanism	Stainless Steel Barb
Tensile Strength	40 pounds ; 180 newtons

### European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	3.6mm
Length belt/tape/tie	138mm
Tie thickness	1.3mm
Max. bundle diameter	35mm
Min. holding force	180N
Operating temperature	-40-+105°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Green
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y

### Packaging

Inner Quantity	1000
Inner Dimensions (inches)	12x12x0
Outer Quantity	10000
Outer Dimensions (inches)	13.3x11.1x11
Weight Uom	1.43 lbs. per 1000

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000494
--------------------------------	-----------

