



Catalog Number: TYH272M
Product ID: 7TCG009590R0008
UPC Number: 78621052008
EAN Number: 05414363067443
Status: A



Cable Tie, Heat Stabilized Polyamide (Nylon 6.6) - Greenish Tint, for Temperatures up to 105 Degrees Celsius (220 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 222mm (8.74 Inches), Width of 7.6mm (0.30 Inches), Thickness of 1.6mm (0.063 Inches), Tensile Strength Rating of 540 Newtons (120 Pounds)

- Application Tools: ERG120, WT197

Actual

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	Heat-Stabilized
Standard	UL E49405
Width	0.275 in ; 6.99 mm
Length	8.75 in ; 225.25 mm
Bundle Diameter	2 in ; 50.8 mm
Material	Nylon/Polyamide 6.6
Color	Green Tint
Tensile Strength	120 pounds ; 540 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	7.6mm
Length belt/tape/tie	222mm
Tie thickness	1.6mm
Max. bundle diameter	50mm
Min. holding force	540N
Operating temperature	-40-+105°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Green
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y

Packaging

Inner Quantity	500
Outer Quantity	5000
Outer Dimensions (inches)	19.7x10.2x13.8
Weight Uom	3.13 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

