



Actual

**Catalog Number:** TYM5412X-S  
**Product ID:** 7TAG009550R0028  
**UPC Number:** 78621084005  
**EAN Number:** 05414363067603  
**Status:** A

Messenger Hanger and Hanger Strap-Releasable, Black Nylon 12 for Temperatures up to 80 Degrees Celsius (176 F), Weather and Ultraviolet Resistant, Stainless Steel Hook, Length of 304.8mm (12.0 Inches), Width of 13.21mm (0.520 Inch), Tensile Strength Rating of 890 Newtons (200 Pounds)

### North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	Messenger Hanger Strap
Width	0.52 in ; 13.21 mm
Length	12 in ; 304.8 mm
Bundle Diameter	3 in ; 76.2 mm
Material	Nylon/Polyamide 12
Color	Black
Tensile Strength	200 pounds ; 890 newtons

### European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	13.21mm
Length belt/tape/tie	304.8mm
Max. bundle diameter	76.2mm
Min. holding force	890N
Material	Metal
Material quality	Polyamide PA
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N

### Packaging

Inner Quantity	50
Outer Quantity	250
Outer Dimensions (inches)	23x16x10
Weight Uom	6.38 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website