



Actual

Catalog Number: TYM5418X-S
Product ID: 7TAG009550R0030
UPC Number: 78621084009
EAN Number: 05414363067627
Status: A

Messenger Hanger and Hanger Strap-Releasable, Black Nylon 12 for Temperatures up to 80 Degrees Celsius (176 F), Weather and Ultraviolet Resistant, Stainless Steel Hook, Length of 457.2mm (18.0 Inches), Width of 13.21mm (0.520 Inch), Tensile Strength Rating of 890 Newtons (200 Pounds)

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	Messenger Hanger Strap
Width	0.52 in ; 13.21 mm
Length	18 in ; 457.2 mm
Bundle Diameter	Max 5 in ; Max 127 mm
Material	Nylon/Polyamide 6.6
Color	Black
Tensile Strength	200 pounds ; 889 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	13.21mm
Length belt/tape/tie	457.2mm
Min. holding force	890N
Material	Metal
Material quality	Polyamide PA
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N

Packaging

Inner Quantity	25
Outer Quantity	100
Outer Dimensions (inches)	24x8.2x8.8
Weight Uom	15 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website