



Actual

Englewood Electric

Catalog Number: TYPEA38-250
Product ID: 7TAD012540R0003
UPC Number: 78621097669
EAN Number: 05414363183044
Status: A

3/8 Inch Non-metallic Orange Type A Liquidtight Conduit

- Smooth, seamless inner core of flexible PVC that is bonded to a coursing of flexible PVC. Between these layers is a woven nylon mesh molded for reinforcement.
- Sunlight resistant
- Meets NEC, article 351, part "B" (ANSI/NFPA-70) for flexible liquidtight non-metallic conduit.

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Type	Type A-Non-Metallic Liquidtight Conduit
Special Features	No Metal Core to Fatigue from Flexing or Vibration
Application	Ideally Suited for Continuous Flexing Applications or Vibration
Standard	UL E95745
Trade Size	3/8 in
Length	250 ft
Material	PVC
Color	Orange

European Specifications (ETIM)

ETIM	EC001177 Protective plastic hose
Nominal size in inch	3/8 inch
Material	PVC
Sheathing material	Other
Operating temperature	-20-+60°C
UV resistant	Y
Flexibility	Flexible
Colour	Orange
Approved according to CSA	Y

Packaging

Outer Quantity	250
Outer Dimensions (inches)	35x35x7
Weight Uom	16.38 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000172
--------------------------------	------------