

Catalog Number: TYR508
Product ID: 7TAG009540R0002
UPC Number: 78621080646
EAN Number: 05414363067740
Status: A



Reuseable Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 364mm (14.343 Inches), Width of 4.83mm (0.19 Inches), Thickness of 1.40mm (0.055 Inches), Tensile Strength Rating of 220 Newtons (50 Pounds)

Actual

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5045 Releasable Ties
Type	Reusable
Width	0.19 in ; 4.83 mm
Length	14.33 in ; 364 mm
Thickness	0.055 in ; 1.4 mm
Bundle Diameter	0.39 to 4.01 in ; 10 to 102 mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Double Locking Head
Tensile Strength	50 pounds ; 220 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.83mm
Length belt/tape/tie	364.3122mm
Tie thickness	1.4mm
Max. bundle diameter	102mm
Min. holding force	220N
Operating temperature	-40-+85°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y

Packaging

Inner Quantity	100
Inner Dimensions (inches)	17.4x5.95x2.1
Outer Quantity	500
Outer Dimensions (inches)	17.4x5.95x5.7
Weight Uom	5.09 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Catalog Page

Available on Website