



Catalog Number: TYS6-280C
Product ID: 7TAG009450R0207
UPC Number: 78621091533
EAN Number: 05414363067979
Status: A



Multi-Lok 316 Stainless Steel Cable Tie, Black Nylon 11 Coated for High Temperature Applications, Weather and Ultraviolet Resistant, Length of 150mm (5.9 Inches), Width of 7mm (0.28 Inch), Thickness of 0.4mm (0.02 Inch), Tensile Strength Rating of 1112 Newtons (250 Pounds)

- Application Tools: WTAE200, WTAE201,

Actual



North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5046 Stainless Steel Ties
Type	Stainless Steel
Standard	UL E49405
Width	0.28 in ; 7 mm
Length	5.9 in ; 150 mm
Thickness	0.02 in ; 0.4 mm
Material	316 Stainless Steel
Color	Black
Lock Mechanism	Multi-Lok
Tensile Strength	250 pounds ; 1112 newtons

Actual

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	7mm
Length belt/tape/tie	150mm
Tie thickness	0.4mm
Max. bundle diameter	45mm
Min. holding force	1112N
Operating temperature	-40-+150°C
Model	Internal toothing
Band closure	Ball latch
Material	Metal
Material quality	Stainless steel 316 (V4A)
Surface protection	Plastic-coated
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y

Packaging

Inner Quantity	100
Outer Quantity	1000
Outer Dimensions (inches)	11x8.5x7.5
Weight Uom	8.13 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000433
--------------------------------	-----------

