



Family

Catalog Number: WE-4-18-6/4-L
Product ID: 7TAG054090R0269
UPC Number: 78621072354
EAN Number: 05414363070856
Status: A

Miniature Striped Cable Tie, Blue/Yellow Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 100.8mm (3.94 Inches), Width of 2.41mm (0.095 Inch), Thickness of 1.13mm (0.045 Inch), Tensile Strength Rating of 80 Newtons (18 Pounds), Maximum Bundle Diameter 18.88mm (0.625 Inch)

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	Miniature Striped
Width	0.095 in ; 2.41 mm
Length	3.94 in ; 100.8 mm
Thickness	0.045 in ; 1.13 mm
Bundle Diameter	Max 0.625 in ; Max 15.88 mm
Material	Nylon/Polyamide 6.6
Color	Striped - Blue ; Yellow
Lock Mechanism	Plastic Pawl
Tensile Strength	18 pounds ; 80 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	2.41mm
Length belt/tape/tie	100.8mm
Tie thickness	1.13mm
Max. bundle diameter	18.88mm
Min. holding force	80N
Operating temperature	-40-85°C
Model	Internal toothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide PA
Halogen free	Y
Colour	Other
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N

Packaging

Inner Quantity	50
Inner Dimensions (inches)	8x4x.5
Outer Quantity	4000
Outer Dimensions (inches)	16.25x8.5x7.5
Weight Uom	0.63 lbs. per 1000