



Representative

**Catalog Number:** X58  
**Product ID:** 7TAD013270R0044  
**UPC Number:** 78621016639  
**EAN Number:** 05415022259162  
**Status:** A

BlueKote Form 8, (X) 1-1/2 Inch Conduit Body, Body Material Gray Iron with Zinc Plating and Baked on Epoxy Powder Coat with BlueKote Internal Coating for Use with Rigid/IMC Conduit

- Eliminates rough internal surfaces that can cut into cable jacket, insulation and conductors during pulling and also reduces installation time and risk of installer strain.
- Triple-layer protection...including two layers of epoxy coating which stops corrosion in its tracks.
- Bodies are designed with a flat back, allowing more cubic inch capacity.
- Conduit bodies make 90 degree bends in conduit runs, act as mounting outlets for wiring devices and lighting fixtures and to provide access to conductors for maintenance and future system changes.

**North American Specifications (UNSPSC)**

UNSPSC	39131708 Electrical conduit fitting body
IGCC	5563 Electrical conduit fitting body
Type	Form 8 Conduit Body
Special Features	BlueKote Teflon Based Internal Finish Provides a Slick, Easy-Glide Internal Surface Which Significantly Lowers the Amount of Force Necessary to Pull Wires.
Application	Conduit Bodies are Installed In Conduit Systems to Connect Sections, Act As Pull Outlets When Conductors are Being Installed and Provide Easy Access for Splices In Branch Conductors.
Standard	UL E2969, CSA
Hub Size	1-1/2 in
Form	Form 8
Material	Gray Iron
Finish	Zinc Plated with Epoxy Powder Coat

**Packaging**

Inner Quantity	1
Inner Dimensions (inches)	9.75x6.75x4.75
Outer Quantity	2
Outer Dimensions (inches)	22.4x6.8x7.1
Weight Uom	6.5 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet US Available on Website

**Header**

3D Model Available on Website