



Catalog Number: XD5NM
Product ID: 7TAA232980R0060
UPC Number: 03448102044
Status: A



Expansion/Deflection Coupling, Size 1-1/2 Inches, Material Schedule 40/80 PVC with Neoprene Rubber Boot and Stainless Steel Clamp

- For use with schedule 40 & 80 PVC rigid conduit to couple sections of conduit & protect wiring systems from damage due to movement.
- Suitable for wet location

Actual



Representative

North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Type	XD Expansion/Deflection Couplings
Special Features	Accommodates Axial Expansion/contraction Up to 3/4 Inch, Parallel Deflection Up to 3/4 Inch and Angular Misalignment Up to 30 Degree.
Application	Bridges, Tunnels, Inter-Building Walkways, Docks and Piers and Wastewater and Water Treatment Facilities
Standard	cULus, CSA C22.2 No. 85, UL E23018
Trade Size	1-1/2 Inch
Outside Diameter	3.6 in
Length	8.26 in
Material	PVC

European Specifications (ETIM)

ETIM	EC000939 Coupler for installation tubes
Material	Plastic
Material quality	PVC
Model	Thread
Two piece	N
With inspection opening and cover	N

Packaging

Outer Quantity	1
Outer Dimensions (inches)	10x4.87x4.87
Weight Uom	1.95 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000230
Marketing Brochure	Available on Website
Video	Available on Website